

Termostat KSD9700 250V/5A, NC, plastični

Šifre proizvoda:

Šifra proizvoda: AM7624

EAN13: -

HS kód: 90321020

Parametri proizvoda:

Trenutno: Max. 5 A

Napetost: 250 V AC

Kontakt: NC (normalno zatvoreno)

Pokriti: IP65



Varijante proizvoda:

Radna temperatura: 15 °C, 20 °C, 25 °C,
30 °C, 35 °C, 40 °C, 45 °C, 50 °C, 55 °C,
60 °C, 65 °C, 70 °C, 75 °C, 80 °C, 85 °C,
90 °C, 95 °C, 100 °C, 105 °C, 110 °C,
115 °C, 120 °C, 125 °C, 130 °C, 135 °C,
140 °C, 145 °C, 150 °C, 155 °C, 160 °C,
165 °C, 170 °C, 175 °C, 180 °C, 185 °C,
190 °C, 195 °C

Opis proizvoda:

Potpuno zatvoren termostat industrijske kvalitete. Otvara se kada se postigne određena temperatura. Na nižim temperaturama termostat se zatvara.

Primjenjivo na sve vrste kućanskih aparata i elektroničkih proizvoda. Na primjer, elektromotori, fluorescentne lampe, punjači baterija, transformatori, solenoidi, grijalice, grijaće prostirke i ostalo.

NC krug (normalno zatvoren)

automatsko resetiranje
radni napon 250V AC/ 125V AC

maks. struja 5A

brzina odziva $\leq 1^{\circ}\text{C}/\text{min}$

otpor strujnog kruga: $\leq 50\text{m}\Omega$

otpor izolacije: $\geq 100\text{M}\Omega$

Vijek trajanja: do 10.000 ciklusa prebacivanja
plastična kutija

lokacija izlaza: radijalna
veličina: 20x7,4x3,8 mm
duljina kabela: 70 mm
cijena za 1 komad

Radno temperatura	Resetiraj temperatura	Radno temperatura	Resetiraj temperatura
25 \pm 5 $^{\circ}\text{C}$	$\geq 15^{\circ}\text{C}$	105 \pm 5 $^{\circ}\text{C}$	75 \pm 15 $^{\circ}\text{C}$
30 \pm 5 $^{\circ}\text{C}$	$\geq 20^{\circ}\text{C}$	110 \pm 5 $^{\circ}\text{C}$	75 \pm 15 $^{\circ}\text{C}$
35 \pm 5 $^{\circ}\text{C}$	$\geq 25^{\circ}\text{C}$	115 \pm 5 $^{\circ}\text{C}$	80 \pm 15 $^{\circ}\text{C}$
40 \pm 5 $^{\circ}\text{C}$	$\geq 30^{\circ}\text{C}$	120 \pm 5 $^{\circ}\text{C}$	85 \pm 15 $^{\circ}\text{C}$
45 \pm 5 $^{\circ}\text{C}$	$\geq 33^{\circ}\text{C}$	125 \pm 5 $^{\circ}\text{C}$	85 \pm 15 $^{\circ}\text{C}$
50 \pm 5 $^{\circ}\text{C}$	$\geq 35^{\circ}\text{C}$	130 \pm 5 $^{\circ}\text{C}$	90 \pm 15 $^{\circ}\text{C}$
55 \pm 5 $^{\circ}\text{C}$	42 \pm 6 $^{\circ}\text{C}$	135 \pm 5 $^{\circ}\text{C}$	95 \pm 15 $^{\circ}\text{C}$
60 \pm 5 $^{\circ}\text{C}$	48 \pm 10 $^{\circ}\text{C}$	140 \pm 5 $^{\circ}\text{C}$	100 \pm 15 $^{\circ}\text{C}$
65 \pm 5 $^{\circ}\text{C}$	48 \pm 10 $^{\circ}\text{C}$	145 \pm 5 $^{\circ}\text{C}$	100 \pm 15 $^{\circ}\text{C}$
70 \pm 5 $^{\circ}\text{C}$	50 \pm 12 $^{\circ}\text{C}$	150 \pm 5 $^{\circ}\text{C}$	105 \pm 15 $^{\circ}\text{C}$
75 \pm 5 $^{\circ}\text{C}$	53 \pm 14 $^{\circ}\text{C}$	155 \pm 5 $^{\circ}\text{C}$	110 \pm 15 $^{\circ}\text{C}$
80 \pm 5 $^{\circ}\text{C}$	55 \pm 15 $^{\circ}\text{C}$	160 \pm 5 $^{\circ}\text{C}$	115 \pm 15 $^{\circ}\text{C}$
85 \pm 5 $^{\circ}\text{C}$	60 \pm 15 $^{\circ}\text{C}$	165 \pm 5 $^{\circ}\text{C}$	115 \pm 15 $^{\circ}\text{C}$
90 \pm 5 $^{\circ}\text{C}$	65 \pm 15 $^{\circ}\text{C}$	170 \pm 5 $^{\circ}\text{C}$	120 \pm 15 $^{\circ}\text{C}$
95 \pm 5 $^{\circ}\text{C}$	70 \pm 15 $^{\circ}\text{C}$	175 \pm 5 $^{\circ}\text{C}$	125 \pm 15 $^{\circ}\text{C}$
100 \pm 5 $^{\circ}\text{C}$	70 \pm 15 $^{\circ}\text{C}$	180 \pm 5 $^{\circ}\text{C}$	130 \pm 15 $^{\circ}\text{C}$

Galerija:

